

LP Morgan HideAway User Manual



LP Morgan HideAway Manual

Congratulations on purchasing the LP Morgan HideAway!

ATTENTION:

Please read the instructions before beginning your installation

1. You will need a cutout in your ceiling - depending on the size of your HideAway (double check the size first!):

Product Code	HideAway	Box Details Length (a) x Width (b) x Height (c)	Ceiling Cutout Size	To Suit Rondo Screen Size
LPM30HID220	A	2200 x 194 x 160	2205 x 200	72V, 84V, 72H, 74W
LPM30HID256	B	2560 x 194 x 160	2565 x 200	90V, 100V, 82H, 92H, 85W, 94W
LPM30HID298	C	2975 x 194 x 160	2980 x 200	120V, 100H, 110H, 95CS, 100CS, 105CS, 103W, 113W

2. The side of the box marked "Viewing side" faces the projector.
3. The mounting brackets for the HideAway box are secured at both ends for easy installation.
4. Hang the HideAway so that the Aluminium Trim is flush with the underside of the ceiling.
5. When you have secured the HideAway box in the ceiling, open the access panel and hang your LP Morgan Rondo Screen on the brackets supplied inside. (For A, B & C sizes only).
6. Follow the instructions supplied with your screen for the correct wiring diagram. Standard motorised screens will require an electrician to complete the installation.
7. Test that the screen operates correctly, and set the limits, if required. Follow the instructions supplied with your screen to do this.
8. Screen should always retract to the Upper Limit previously set by the factory as the default position. The fabric should not be exposed when in the closed position

Cleaning and Maintenance

1. The HideAway fascia can be cleaned with a mild detergent, water and a soft cloth to wash off any marks. Rinse and dry with a clean cloth or towel.
2. Refer to your LP Morgan Rondo Instructions for details on cleaning your screen surface.

Warranty information

Keep your original receipt for warranty.

Please fill out the online warranty form in order to qualify for the manufacturer's warranty.

<http://www.lpmorgan.com.au/owners.html>

The warranty covers defects in workmanship and materials, provided this product has been installed in a normal environment and maintained according to the written instructions. Herma warrants the product against loss of usefulness, discolouration or deterioration of optical quality within the warranty period as a result of manufacturing or material defects. This warranty applies only within Australia.

Please return your goods to the place of purchase for all warranty claims.

Conditions

Any equipment replaced pursuant to the terms of this warranty shall be retained by Herma.

All costs related to de-installation and re-installation of the product covered by this warranty are not the responsibility of Herma Technologies. Herma will not be responsible for any consequential damages during or following installation procedures.

Herma is not responsible for any freight costs relating to repair or replacement. Equipment must be returned to Herma in suitable packing to prevent damage in transit. Herma will not accept any responsibility for damage to the equipment caused by inadequate or unsuitable packing, or for any damage howsoever caused whilst the goods are in transit.

Herma Technologies shall not be liable for any injury, loss or damage, direct or consequential, arising out of the use of, misuse of, or inability to use, the equipment.

This Warranty does not cover any product which has been subjected to misuse, abuse, neglect, accidental or intentional damage, improper voltage or any alteration which affects the reliability or performance of the equipment not attributable to faulty manufacture, parts or labour and without limiting the generality of the foregoing.

This Warranty does not cover any product where usage, adaptation or installation are not in accordance with our written installation and operating instructions.

Warranty Period:

Two years from date of purchase.

**For more information on our range of products,
please visit www.lpmorgan.com.au, or contact
your local LP Morgan Retailer.**

Information in this document is subject to change without notice.

© Herma Technologies. All rights reserved.

This document is protected against unauthorised copying electronic or otherwise.

Trademarks used in this text: Herma, the Herma Logo, Galleria, LP Morgan and LP Morgan logo are registered trademarks of Herma Technologies.

Other trademarks and trade names used in this document remain the property of the relevant owners.

October 2011 Version 2.3

Factory 4a, 6 Albert Street Preston Vic 3072

Phone: +61 3 9480 6233 **Fax:** +61 3 9480 6533

Email: info@herma.com.au www.lpmorgan.com.au

